

# Product sheet



## LEGRAND

Resistance heater - for enclosure - pulsated air 230 V~  
- 150 W

REF. 035310 | EAN. 3245060353100

---

> [Visit e-catalogue](#)

## Product characteristics

- Heat regulation for cabinets and enclosures - heating and regulation
- Heating - IP 20 - Class II - Prevent condensation forming inside the enclosure «PTC» auto - regulated and self - limited surface temperature - Connection on terminals - Mounting on rail - Heat dissipator in aluminium under plastic UL 94 VOPulsated air resistance heaters 230 V~ - Built - in temperature limiter - Material : Polycarbonate UL 94 VO - Power : 150 W - Start - up current : 12 A - Thermostat : Without 0 to 60 °C with LED - Fan flow rate : 13 m<sup>3</sup>/h

## Documentation

---

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0444.pdf](#) | PDF (0.12Mo)

 [ex223001\\_0443.pdf](#) | PDF (0.1Mo)