


Product sheet



LCS³ LEGRAND

6 connectors RJ45 Category 6A STP

REF. 033775 | EAN. 3414970870759

This RJ45 connector is to be installed in flat or angled (1U 24 and 48 slots) patch panels. Front-panel and fast-snap accessibility of each individual connector provide ease and reliability for tool-less installation and maintenance.

> [Visit e-catalogue](#)

Description

This RJ45 connector is to be installed in flat or angled (1U 24 and 48 slots) patch panels. Front-panel and fast-snap accessibility of each individual connector provide ease and reliability for tool-less installation and maintenance.

Product characteristics

- 568 A/B marking
- POE + compliant

Recommendation / Restriction

- Compliant with ISO/IEC 11801 edition 3.0 (2017) and EIA/TIA 568 C2-1 standards

The product's benefits

Installation

- User installation is rendered easy through an intuitive fast and secure management of each individual connector.

Usage

- Daily user maintenance is rendered easy through the move-add-change management of each cassette and individual connector.

Avantages

- Connector tested and guaranteed to support POE signals (standard IEEE 802.3af and POE+, draft standards 802.3at) up to 2500 connections and disconnections with load.
- Tests are carried out with 2 simultaneous POE+ circuits producing a minimum total power of 50W.

Documentation

TECHNICAL DOCUMENTATION

-  S000096850FR-06.pdf | PDF (8.19Mo)
-  S000096850EN-06.pdf | PDF (8.19Mo)
-  LE09819AB.pdf | PDF (1.07Mo)

Agreements & Certificates

-  AoC-PL2_Cat6A_FFTP_32799_ac1171009 | (0.07Mo)
-  AoC-CL4_Cat6A_STP_32869_ac1181045 | (0.08Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0979.pdf | PDF (0.13Mo)
-  ex223001_0982.pdf | PDF (0.08Mo)

	AoC-PL2_Cat6A_FTP_32778_ac1171014 (0.08Mo)
	AoC-4PPoE 2019-676 Ac Delta Force (0.08Mo)
	LGRP-00626-V02.01-FR.pdf PDF (0.96Mo)
	AoC-PL2_Cat6A_STP_32777_ac1171017A (0.08Mo)
	AoC-CL2_Cat6A_STP_32777_ac1171018A (0.08Mo)
	AoC-CL2_C6A_UFTP_32884_ac1191059 (0.06Mo)
	AoC-CL2_C6A_STP_32882_ac1191063 (0.06Mo)
	AoC-CL2_Cat6A_FFTP_32799_ac1171010 (0.07Mo)
	AoC-CL4_Cat6A_STP_32778_ac1181044 (0.08Mo)
	AoC-Composant Cat6A STP 3P-1200331 (0.06Mo)
	AoC-CL2_C6A_FFTP_32883_ac1191061 (0.06Mo)
	AoC-CL2_Cat6A_FTP_32778_ac1171015 (0.08Mo)
	AoC-PL3_Cat6A_FTP_32778_ac1171016 (0.08Mo)
	AoC-PL2_C6A_FFTP_32883_ac1191060 (0.06Mo)
	LGRP-00626-V02.01-EN.pdf PDF (0.95Mo)
	AoC-PL3_Cat6A_STP_32777_ac1171019A (0.08Mo)
	AoC-PL2_C6A_STP_32882_ac1191062 (0.06Mo)
	AoC-PL3_Cat6A_FFTP_32799_ac1171011 (0.07Mo)
	AoC-PL2_C6A_UFTP_32884_ac1191058 (0.06Mo)