

Product sheet



LCS³ LEGRAND

On field RJ45 Plug category 6A STP toolless

REF. 033749 | EAN. 3414971464360

This cat. 6A STP RJ45 plug facilitates on-field wiring of four twisted pairs data cables thanks to toolless connection. It's ideal for a link terminated with a plug on active equipment side, notably CCTV camera and Wi-Fi access points.

> [Visit e-catalogue](#)

Description

This cat. 6A STP RJ45 plug facilitates on-field wiring of four twisted pairs data cables thanks to toolless connection. It's ideal for a link terminated with a plug on active equipment side, notably CCTV camera and Wi-Fi access points.

Product characteristics


- Category 6A STP
- Compatible for links cat 5/Class D, cat6/Class E and Cat6A/Class EA. For shielded and unshielded cables.
- Toolless connection
- Compact

Recommendation / Restriction

- For round cables with outer diameter between 6 and 7,5 mm and AWG23 to AWG26 (solid or stranded)

Documentation

TECHNICAL DOCUMENTATION

 S000104439EN-04.pdf | PDF (0.23Mo)

 LE11075AD.pdf | PDF (0.62Mo)

 S000104439FR-04.pdf | PDF (0.23Mo)

Agreements & Certificates

 LGRP-01964-V01.01-EN.pdf | PDF (0.86Mo)

 LGRP-01964-V01.01-FR.pdf | PDF (0.83Mo)

The product's benefits

Installation

- This cat. 6A STP RJ45 plug facilitates on-field wiring of four twisted pairs data cables thanks to toolless connection (no need for RJ crimping tool).

Usage

- With Modular Plug Terminated (MPT) for CCTV camera and Wi-Fi access points connections, no risk for accidental disconnection that can occur with RJ45 sockets and patchcords.

Avantages

- The plug can be reused up to 20 times.

CATALOGUE PAGE & OTHERS

 ex223001_0982.pdf | PDF (0.08Mo)