

# Product sheet



LCS<sup>3</sup> LEGRAND

Set of 12 OS2 LC-UPC pigtails for fibre optic 9/125µm 1 m

REF. 032624 | EAN. 3245060326241

Singlemode pigtails are used in high speed telecommunication and data transmission networks as well as in metro and access networks. OS2 singlemode pigtails are terminated with standard connectors for optimum optical performance.

> [Visit e-catalogue](#)

## Description

Singlemode pigtails are used in high speed telecommunication and data transmission networks as well as in metro and access networks. OS2 singlemode pigtails are terminated with standard connectors for optimum optical performance.

### Product characteristics

- OS2 single-mode 9/125µm
- LC - UPC connectors
- 1 meter length
- 900 µm tight buffer and easy strip
- Low smoke zero halogen (LSZH) sheath

### Recommendation / Restriction

- OS1/OS2 fibre conforms to ITU-G652.D and TIA/EIA standards 492CAAA

## Documentation

### TECHNICAL DOCUMENTATION

- S000082752EN-04.pdf | PDF (0.93Mo)
- S000082752EN-00.pdf | PDF (0.37Mo)
- S000082752FR-04.pdf | PDF (0.96Mo)

## The product's benefits

### Installation

- Easy strip for on-site installation

### Usage

- Supports high speed multi-channel video networks, metro voice and data services and access networks

### CATALOGUE PAGE & OTHERS

- ex223001\_1003.pdf | PDF (0.12Mo)