

Product sheet



LEGRAND

Line tap - non-shear - with feet - capacity per tap 2x75 mm² - hexagonal head

REF. 034045 | EAN. 3245060340452

> [Visit e-catalogue](#)

Product characteristics

- Line taps and equipotential bonding connectorsLine tapsNon-shear line taps- Hexagonal head - With feet - Capacity per tap : 2 x 75 mm²- Width of slot : 11.7 max. cable Ø in mm- Overall height : 71 mm- Fixing centres : 62 mm

Documentation

TECHNICAL DOCUMENTATION

 F00003-01fr.pdf | PDF (0.04Mo)

 F00003-01en.pdf | PDF (0.04Mo)

 0064U92-01.pdf | PDF (0.01Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0820.pdf | PDF (0.22Mo)