

Product sheet



LEGRAND

Line tap - non-shear - w/o feet - capacity per tap 2x25 mm² - hexagonal head

REF. 034033 | EAN. 3245060340339

> [Visit e-catalogue](#)

Product characteristics

- Line taps and equipotential bonding connectorsLine tapsNon-shear line taps- Hexagonal head - Without feet - Capacity per tap : 2 x 25 mm²- Width of slot : 7.4 max. cable Ø in mm- Overall height : 49 mm

Documentation

TECHNICAL DOCUMENTATION

 F00003-01fr.pdf | PDF (0.04Mo)

 F00003-01en.pdf | PDF (0.04Mo)

 0064U92-01.pdf | PDF (0.01Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0820.pdf | PDF (0.22Mo)