

Product sheet



NYLBLOC™ LEGRAND

Connection strip Nylbloc - capacity 6 mm² - max. current 41 A - white

REF. 034223 | EAN. 3245060342234

> [Visit e-catalogue](#)

Product characteristics

- Nylbloc™ - connection strips and connectors without screws Nylbloc connection strips - 12 elements with captive screws - Supplied with screws undone - Flame retardant polypropylene (– 25 °C to + 100 °C) - Ambient temperature from – 25 °C to + 55 °C (T 55) - Conform to EN 60998 - 2 - 1 and EN 60664 - 1 - Self - extinguishing to EN 60695 - 2 - 11 at 850° - Insulation voltage : 250 V according to EN 60 998 - 2 - 1 - Use at 400 V integrated in a series of products that comply with the requirements of EN 60664 - 1, pollution degree 2, overload category III - White - Rated capacity : 6 mm²mm² - Hole Ø : 3.5 mm - Max current : 41 A

Documentation

CATALOGUE PAGE & OTHERS

 ex223001_0819.pdf | PDF (0.1Mo)

Agreements & Certificates

 LGRP-2015-037-V1-EN.pdf | PDF (0.62Mo)

 AENOR-030/000810 | (0.62Mo)

 IMQ-EN641 | (0.62Mo)

 NF App Domestic-650672A | (0.18Mo)