

Product sheet



MARINA LEGRAND

Marina 820x610x300mm - IP66 IK10 - glass door

REF. 036281 | EAN. 3245060362812

> [Visit e-catalogue](#)

Product characteristics

- IP 66 according to the standard EN/IEC 60529 : completely protected against dust and against jets of water of similar force to heavy seas
- Excellent resistance to corrosion and chemical agents : 1500h resistance to salt spray
- One-piece molded body, reversible cabinet
- RAL 7035 suitable for industrial environments

Recommendation / Restriction

- Recommended for industrial environments with aggressive constraints : corrosion and harsh weather conditions.

The product's benefits

Installation

- Double-bar lock. Equipped with universal lugs at the rear of the cabinets to facilitate the installation of accessories Autocentric of equipments

Usage

- Can be equipped with a wide range of dedicated accessories : plain or perforated plates, plinths, cable-entry plates, plain or glass doors, etc.

Documentation

TECHNICAL DOCUMENTATION

-  EXB22009_Flipbook_FR_(03_2022).pdf | PDF (6.2Mo)
-  F00635FR-04.pdf | PDF (3.05Mo)
-  F00635EN-04.pdf | PDF (3.02Mo)
-  EXB22010_Flipbook_EN_(03_2022).pdf | PDF (6.56Mo)
-  LE08303AA-01.pdf | PDF (1.32Mo)

CAD & Design specs / BIM

-  036281.dwg | DWG (0.18Mo)
-  Legrand-Industrial_enclosures-Polyester-Marina_cabinets-Glass_door.rfa | RFA (0.97Mo)
-  Legrand-Enveloppes_industrielles-Polyester-Coffrets_Marina-Porte_vitree.rfa | RFA (0.97Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0428.pdf | PDF (0.39Mo)
-  ex223001_0426-0427.pdf | PDF (0.36Mo)
-  ex223001_0422.pdf | PDF (0.21Mo)

Agreements & Certificates

-  VERITAS (BV)-07327/E0 BV | (0.59Mo)
-  OC / CB-FR 716848 | (0.38Mo)