

Product sheet



LEGRAND

Atlantic metal cabinet - vertical version - 500 x 400 x 160 mm - 1 door

REF. 036913 | EAN. 3414970696472

> [Visit e-catalogue](#)

Product characteristics

- Atlantic metal cabinets supplied with plain plate - IP 55/IP 66 - IK 10 - Type 4x - Type 12 - IP 66 according to standards IEC EN 60529 for 1 - door cabinets - IP 55 according to standards IEC EN 60529 for 2 - door cabinets - IK 10 according to standards IEC EN 62262 - LCIE 17 07 90 10A - Type 4x, 1 door, Type 12, 2 doors - cULus, Bureau Veritas - EMC attenuation 20 dB (for an EMC attenuation from 40 to 50 dB at 1 GHz, please consult us) - Excellent resistance to corrosion and chemical agents - 80 m thick textured polyester coating. Anti - corrosion treatment for hinges and pins - Reversible door - Fitted with lever - Supplied with double bar lock - Self - centering positioning system for the equipment - Compatible with all Atlantic Accessories Low cable entries RAL 7035 - Optional depth adjustment for cabinets 400 mm depth, with slide rails Cat.No 0 367 45
- Metal door cabinets - Supplied with plain plateVertical version - External dimensions Height x Width x Depth : 500 x 400 x 160 mm - Number of doors : 1 - Weight : 10,3 kg

Documentation

TECHNICAL DOCUMENTATION

- LE08301AA-01.pdf | PDF (0.77Mo)
- EXB22009_Flipbook_FR_(03_2022).pdf | PDF (6.2Mo)
- F02118FR-03.pdf | PDF (5.41Mo)
- F02118EN-03.pdf | PDF (5.4Mo)
- EXB22010_Flipbook_EN_(03_2022).pdf | PDF (6.56Mo)

CAD & Design specs / BIM

- Legrand_Atlantic_vertical_version_references_036910_to_036950.rfa | RFA (3.9Mo)
- Legrand_Atlantic_version_verticale_références_036910_à_036950.rfa | RFA (3.9Mo)
- 036913.dwg | DWG (0.07Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0420-0421.pdf | PDF (0.28Mo)
- ex223001_0416.pdf | PDF (0.06Mo)

Agreements & Certificates

- OC / CB-FR703246 | (0.59Mo)
- TUV GS-R 60175536 | (1.67Mo)
- UL listed cULus-E164087-19951122 | (0.84Mo)
- LGRP-2015-020-V1-EN.pdf | PDF (0.61Mo)
- VERITAS (BV)-03212/J0 BV | (0.59Mo)