

Product sheet



VIKING 3 LEGRAND

Connecting terminal block, screw connection, 1 connection 1entry/1outlet, Cross-section 4mm² - pitch 6mm - green

REF. 037177 | EAN. 3245060371777

> [Visit e-catalogue](#)

Product characteristics

- Green terminal blocks are recommended for protection conductor class II equivalent assemblies.
- 2 areas for automatic insertion bridging combs up to 8mm pitch (upper level only for multi-level terminal blocks)
- Easy insertion of conductors thanks to the ergonomic shape of the entry and outlet.

Recommendation / Restriction

- Installation recommended for electrical connection in industrial and tertiary cabinets and enclosures.

The product's benefits

Installation

- A securing pin on the insulating body holds the Viking 3 terminal blocks together for ease of handling and perfect alignment on the rail. The assembly/disassembly of a terminal block is still possible without removing the adjacent terminal blocks

Usage

- Terminal blocks have two marking zones per level allowing a clear, visible and convenient identification of the circuit. Compatible with CAB 3 marking systems.

Documentation

TECHNICAL DOCUMENTATION

-  F00671EN-02.pdf | PDF (1.11Mo)
-  F00902FR-04.pdf | PDF (1.79Mo)
-  F00902EN-03.pdf | PDF (3.41Mo)
-  F00671FR-02.pdf | PDF (1.08Mo)

CAD & Design specs / BIM

-  037177.dwg | DWG (0.09Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0458.pdf | PDF (0.16Mo)
-  ex223001_0465.pdf | PDF (0.06Mo)
-  ex223001_0466.pdf | PDF (0.13Mo)

Agreements & Certificates

-  UL recogn-20101029-E60900 | (0.13Mo)
-  ATEX-LCIE 16 ATEX 3049U - 02 | (0.71Mo)
-  VERITAS (BV)-23393/C0 BV | (0.61Mo)

-  IMQ-CA02.04206 | (0.87Mo)
-  NF App Domestic-NF208_1010 | (0.28Mo)
-  Ex-002/j | (0.22Mo)