

Product sheet



LEGRAND

Break glass emergency box-2 position-surface mounting-IP44-red box with LED

REF. 038024 | EAN. 3245060380243

> [Visit e-catalogue](#)

Product characteristics

- Safety boxes 125 series - for emergency applications
- Break glass emergency boxes - Polycarbonate, Class II - IK 07 - Equipped with : - hinged glass door with locking option by key - 3 cable entries for CG ISO 16/20 (by top or bottom as reversible product) - 2 entries from back of product 20 - 2 side entries for mini - trunking 20 x 12.5 and 32 x 12.5 - 1 NC contact and 1 NO contact - Breaking capacity : - 400 V~ / 4.5 A - 230 V~ / 6 A - 48 V DC / 1 A - 24 V DC / 1.5 A - Flush-mounting option with boxes 85 - Dim. : 125 x 125 x 71 mm (surface - mounting) IP 44 - 125 x 125 x 33 mm (flush-mounting) IP 30 - Red boxes can be used for fire applications and manipulated by fire fighters - Yellow boxes can be used for emergency applications and manipulated by employees2 - position boxes - Equipment : - 1 mushroom head button for pressing - 1 finishing accessory for simple action release (glass break) or double action (glass break followed by pressing on mushroom head) - 2 long life 230 V~ LED indicators (green/red) - Red box with LED

Documentation

TECHNICAL DOCUMENTATION

→ 4065488-05.pdf | PDF (0.94Mo)

📄 F00029FR-00.pdf | PDF (1.64Mo)

Agreements & Certificates

📄 LGRP-00105-V02.01-EN.pdf | PDF (0.64Mo)

📄 LGRP-00105-V02.01-FR.pdf | PDF (0.64Mo)

CATALOGUE PAGE & OTHERS

📄 ex223001_0920.pdf | PDF (0.05Mo)