

Product sheet



LEGRAND

Bell - for industrial and alarm use - IP44 - IK10 - 24 V~
- Ø150 mm gong

REF. 041416 | EAN. 3245060414160

> [Visit e-catalogue](#)

Product characteristics

- Bells for industrial and alarm use
- Class I - Double insulated - Polyester corrosion resistant finish - 200 hours maxi. continuous rating IP 44 - IK 10 - 150 mm gong - RAL 7037 Grey - Voltage : 24 V~ - Consumption : 360 mA - Average acoustic output at 1 m : 98 dB - Weight : 1 kg

Documentation

TECHNICAL DOCUMENTATION

→ [4065873-00.pdf](#) | PDF (0.21Mo)

Agreements & Certificates

 [LGRP-00530-V01.02-EN.pdf](#) | PDF (0.58Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0551.pdf](#) | PDF (0.1Mo)