

# Product sheet



## LEGRAND

Bell - for industrial and alarm use - IP44 - IK10 230 V~  
- Ø150 mm gong

REF. 041419 | EAN. 3245060414191

> [Visit e-catalogue](#)

## Product characteristics

- Bells for industrial and alarm use
- Class I - Double insulated - Polyester corrosion resistant finish - 200 hours maxi. continuous rating IP 44 - IK 10 - 150 mm gong - RAL 7037 Grey - Voltage : 230 V~ - Consumption : 50 mA - Average acoustic output at 1 m : 98 dB - Weight : 1 kg

## Documentation

### TECHNICAL DOCUMENTATION

→ [4065873-00.pdf](#) | PDF (0.21Mo)

### Agreements & Certificates

 [LGRP-00143-V01.01-EN.pdf](#) | PDF (0.61Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0551.pdf](#) | PDF (0.1Mo)