

Product sheet



MOSAIC LEGRAND

Sounder - IP41 - IK04 - 70 dB - 12/24/48 V - white

REF. 041507 | EAN. 3245060415075

> [Visit e-catalogue](#)

Product characteristics

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Sounders - Conform to EN 54 - 3 standard and CE CPR approved - IP 41 - IK 04 - Mosaic device - 2 modules - Sound level : 70 dB at 2 meters - NF S 32 - 001 sound - Voltage range : 10 - 42 V - Average consumption : 12 V DC 5 mA - 24 V DC 9 mA

Documentation

TECHNICAL DOCUMENTATION

→ [LE02952AB.pdf](#) | PDF (0.97Mo)

Agreements & Certificates

 [NFSSI Composant-DS 015 A2](#) | (0.26Mo)

 [LGRP-2015-223-V1-FR.pdf](#) | PDF (0.61Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0921.pdf](#) | PDF (0.05Mo)