

Product sheet



LEGRAND

Electromechanical siren - IP30 - IK05 - 12 V= - 11 W - 889 mA

REF. 041532 | EAN. 3245060415327

> [Visit e-catalogue](#)

Product characteristics

- Electromechanical and electronic sirens
- Electromechanical sirens IP 30 - IK 05 - Supplied with screws for semi - flush mountingD.C. current - Voltage : 12 V= - Power : 11 W - Consumption : 889 mA - Average acoustic output at 1 m : 98 dB - Weight : 0,2 kg - Max. continuous rating : 200 hr

Documentation

TECHNICAL DOCUMENTATION

→ [4065212-04.pdf](#) | PDF (0.1Mo)

Agreements & Certificates

 [LGRP-2015-321-V1-FR.pdf](#) | PDF (0.62Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0551.pdf](#) | PDF (0.1Mo)

 [ex223001_0533.pdf](#) | PDF (0.07Mo)