

Product sheet



LEGRAND

Electromechanical siren - IP30 - IK05 - 24 V= - 12 W-
516 mA

REF. 041533 | EAN. 3245060415334

> [Visit e-catalogue](#)

Product characteristics

- Electromechanical and electronic sirens
- Electromechanical sirens IP 30 - IK 05 - Supplied with screws for semi - flush mountingD.C. current - Voltage : 24 V= - Power : 12 W - Consumption : 516 mA - Average acoustic output at 1 m : 100 dB - Weight : 0,2 kg - Max. continuous rating : 200 hr

Documentation

TECHNICAL DOCUMENTATION

→ [4065212-04.pdf](#) | PDF (0.1Mo)

Agreements & Certificates

 [LGRP-2015-321-V1-FR.pdf](#) | PDF (0.62Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0551.pdf](#) | PDF (0.1Mo)

 [ex223001_0533.pdf](#) | PDF (0.07Mo)