

Product sheet



LEGRAND

Electromechanical siren - IP30 - IK05 - 110 V~ - 70 W-
400 mA

REF. 041538 | EAN. 3245060415389

> [Visit e-catalogue](#)

Product characteristics

- Electromechanical and electronic sirens
- Electromechanical sirens IP 30 - IK 05 - Supplied with screws for semi - flush mountingA.C. current - 50/60 Hz - Voltage : 110 V~
- Power : 70 W - Consumption : 400 mA - Average acoustic output at 1 m : 105 dB - Weight : 0,35 kg - Max. continuous rating :
100 hr

Documentation

TECHNICAL DOCUMENTATION

→ 4065212-04.pdf | PDF (0.1Mo)

Agreements & Certificates

 LGRP-2015-321-V1-FR.pdf | PDF (0.62Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0551.pdf | PDF (0.1Mo)

 ex223001_0533.pdf | PDF (0.07Mo)