

Product sheet



MOSAIC LEGRAND

Sounder beacons - IP21 - IK07 - 90 dB - 12/24/48 V= - white

REF. 040587 | EAN. 3245060405878

> [Visit e-catalogue](#)

Product characteristics

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Sounder beacons - Conform to EN 54 - 3 standard and CE CPR approved - Sound level : 90 dB at 2 meters - NF S 32 - 001 sound - Red flash - Voltage range : 10 - 58 V - Average consumption : 12 V DC 23 mA ; 24 V DC 22 mA ; 48 V DC 23 mA - IP 21 - IK 07 - Flush mounting in false ceiling

Documentation

TECHNICAL DOCUMENTATION

→ [LE02620AC.pdf](#) | PDF (2.63Mo)

Agreements & Certificates

 [NFSSI Composant-DS 034 A2](#) | (0.23Mo)

 [LGRP-00273-V01.01-FR.pdf](#) | PDF (0.62Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0921.pdf](#) | PDF (0.05Mo)