

Product sheet



LEGRAND

Electromagnetic door holder-IK07-Strength 200N-
average consumption 24 V= 77 mA

REF. 040687 | EAN. 3245060406875

> [Visit e-catalogue](#)

Product characteristics

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Electromagnetic door holder - Automatically closes fire doors by current breaking - White metal connection box with electromagnetic element and local push button - Wall surface - mounting - Metal washer hinged for door Fixing - Operating voltage : 24/48 V DC - Average consumption : 24 V DC 23 mA - 48 V DC 45 mA - Power : 0,6 W/ 24 V - 2.2 W/ 48 V - Strength : 200 N (or 20 Kg minimum) - Conform to EN 11 - 55 standard - IK 07

Documentation

TECHNICAL DOCUMENTATION

→ [LE02136AC.pdf](#) | PDF (1.04Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0921.pdf](#) | PDF (0.05Mo)