

# Product sheet



## LEGRAND

Transformer equipt separates mono circuits - prim  
230/400 V/sec 115/230 V - 40 VA

REF. 042785 | EAN. 3245060427856

> [Visit e-catalogue](#)

## Product characteristics

- Power : 40 VA
- Primary flexible cable terminal capacity : 1 to 4 mm<sup>2</sup>.
- Secondary flexible cable terminal capacity : 1 to 4 mm<sup>2</sup>.

## Documentation

### TECHNICAL DOCUMENTATION

-  PRT219022-GT-transfosBT-BT-022020.pdf | PDF (4.27Mo)
-  EXB22028\_GT\_Transformateurs\_BT\_BT\_FR.pdf | PDF (4.83Mo)
-  EXB19045\_TG\_Transformers\_EN.pdf | PDF (4.9Mo)

### Agreements & Certificates

-  LGRP-2015-038-V1-EN.pdf | PDF (0.63Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0504.pdf | PDF (0.04Mo)
-  ex223001\_0499.pdf | PDF (0.06Mo)
-  ex223001\_0495.pdf | PDF (0.11Mo)
-  ex223001\_0502-0503.pdf | PDF (0.06Mo)