

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - PIR 360° lighting sensor 2x12m - IP41 - ceiling mounting

REF. 048817 | EAN. 3245060488178

> [Visit e-catalogue](#)

Product characteristics

- PIR lateral detection 24 m - range 2 x 12 m
- IP41
- Switching control (3 - wire with neutral)
- Standby consumption: 0.4 W
- Connection via automatic terminals

Recommendation / Restriction

- Optimum distance between 2 sensors: 20 m

The product's benefits

Installation

- Precise on-site adjustment using configuration tool Cat.No 0 882 40 Fix directly to a false ceiling with mounting claws (included) or installed in a Batibox box, depth 50 mm, Cat.No 0 893 58 Surface mounted on ceiling using accessory Cat.No 0 488 75

Usage

- Ideal for passage areas with natural light

Advantages

- Can be used with push-button Cat.No 0 770 40 for vacancy mode (manual switch-on and manual or automatic switch-off)
- Fix directly to a false ceiling with mounting claws (included) or installed in a Batibox box, depth 50 mm, Cat.No 0 893 58 Can be surface-mounted in ceiling using accessory Cat.No 0 488 75

Documentation

TECHNICAL DOCUMENTATION

-  LE07602AA.pdf | PDF (9.21Mo)
-  S000072383FR_4.pdf | PDF (3.28Mo)
-  LE04871AB.pdf | PDF (1.51Mo)
-  S000072383EN_3.pdf | PDF (3.3Mo)

CAD & Design specs / BIM

CATALOGUE PAGE & OTHERS

-  ex223001_0891.pdf | PDF (0.05Mo)
-  ex223001_0888.pdf | PDF (0.07Mo)

Agreements & Certificates

 2D-LG-003513.zip | ZIP (0.85Mo)

Legrand_Gestion_eclairage_Detecteur_Presence_Plafond_autonome.rfa | RFA (3.23Mo)

Legrand_Lighting_Management_Standalone_Presence_Sensor_Ceilin g.rfa | RFA (3.23Mo)

 OC / CB-681064A | (1.18Mo)

 LGRP-00389-V02.01-EN.pdf | PDF (0.63Mo)