

# Product sheet



MOSAIC™ LEGRAND

Mosaic™ - PIR 360° motion sensor 8m - IP20 - false ceiling mounting

REF. 048941 | EAN. 3414970595195

> [Visit e-catalogue](#)

## Product characteristics

- PIR detection 360°, range Ø8m at 2.5M heigh
- IP41
- Switching control (3 - wire with neutral)
- Standby consumption: 0.75 W
- Cardboard

## Recommendation / Restriction

- Voltage 230VAC 50/60Hz only Optimum distance between 2 sensors: 6 m

## The product's benefits

### Installation

- Fixes directly to a false ceiling with mounting claws (included)

### Usage

- Ideal for passage areas without natural light

### Avantages

- Cost effective solution
- Automatic switch-on taking into account the ambient light level
- Easy basic settings through a simple screw driver

## Documentation

### TECHNICAL DOCUMENTATION

S000087115FR-4.pdf | PDF (1.69Mo)

LE07906AC.pdf | PDF (1.63Mo)

S000087115EN-2.pdf | PDF (0.97Mo)

### CAD & Design specs / BIM

Autocad Library | ZIP (0.85Mo)

Legrand\_Lighting\_Management\_Standalone\_Motion\_Sensor\_360D\_False\_Ceiling.rfa | RFA (0.52Mo)

Legrand\_Gestion\_eclairage\_Detect\_mvt\_autonome\_360D\_Faux\_Plafo nd.rfa | RFA (0.51Mo)

### CATALOGUE PAGE & OTHERS

ex223001\_0885.pdf | PDF (0.07Mo)

### Agreements & Certificates

OC / CB-685326 | (0.52Mo)

SDoC-L-0374-01A | (0.22Mo)

LGRP-00151-V02.01-EN.pdf | PDF (0.65Mo)