

Product sheet



LEGRAND

PIR compact sensor 1-10V

REF. 048965 | EAN. 3414972095693

> [Visit e-catalogue](#)

Product characteristics

- PIR detection 360°, range Ø7m at 2,5m high
- IP 40
- Dimming 1 - 10V control (up to 10 ballasts)
- switching control 10A
- Standby consumption: 0.3 W

Recommendation / Restriction

- Recommended init operation with configuration tool during installation step

The product's benefits

Installation

- Pluggable connectors to reduce installation time
- Precise on-site adjustment using configuration tool Cat.No 0 882 40

Usage

- Maintained illuminance (dimming in accordance to presence natural light) optimizes user comfort and energy saving

Advantages

- Can be used with push-button Cat.No 0 770 40 for vacancy mode (manual switch-on and manual or automatic switch-off)
- The low profile design means the unit can be mounted in a narrow ceiling void
- Configuration tool managing setting files for product init through preset files, saving and sharing configuration, comparison of product settings

Documentation

TECHNICAL DOCUMENTATION

 S000115118FR_2.pdf | PDF (11.06Mo)

 LE12497AB.pdf | PDF (1.72Mo)

CAD & Design specs / BIM

Legrand_Gestion_eclairage_Detecteur_Presence_Plafond_autonome.rfa | RFA (3.23Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0891.pdf | PDF (0.05Mo)

 ex223001_0889.pdf | PDF (0.06Mo)

Legrand_Lighting_Management_Standalone_Presence_Sensor_Ceilin
g.rfa | RFA (3.23Mo)