

Product sheet



HYPRA LEGRAND

Panel mounting socket Hypra - IP 66/67-55 - 380/415 V~ - 16 A - 3P+N+E - plastic

REF. 051131 | EAN. 3245060511319

> [Visit e-catalogue](#)

Product characteristics

- Hypra IP 66/67 - 55 plastic - increased safety - LV 16 to 125 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP according to IEC 60529 - IK 09 : Plastic - Self - extinguishing : 850°C (support of active parts) / 650°C (plastic housing) LV 380 to 415 V~ 50/60 Hz Panel mounting sockets 3P+N+E - To associate with Cat. No 0 522 29 for surface mounting - To associate with Cat. No 0 522 89 for through wiring surface mounting - 16 A - inclined outlet

Documentation

TECHNICAL DOCUMENTATION

 F00130EN-07.pdf | PDF (1.29Mo)

 F00130FR-07.pdf | PDF (1.5Mo)

CAD & Design specs / BIM

LEGRAND_NON_INTERLOCKED_SOCKETS_FLUSH_MOUNTED_IP66_440.rfa | RFA (0.48Mo)

LEGRAND_NON_INTERLOCKED_SOCKETS_FLUSH_MOUNTED_IP66_400_SYMBOL.rfa | RFA (0.56Mo)

LEGRAND_PRISES_NON_VERROUILLEES_ENCASTREES_IP66_400.rfa | RFA (0.52Mo)

LEGRAND_PRISES_NON_VERROUILLEES_ENCASTREES_IP66_440.rfa | RFA (0.48Mo)

LEGRAND_NON_INTERLOCKED_SOCKETS_SURFACE_MOUNTED_IP66_400.rfa | RFA (0.61Mo)

LEGRAND_PRISES_NON_VERROUILLEES_SAILLIES_IP66_400.rfa | RFA (0.62Mo)

 051131.dwg | DWG (0.11Mo)

LEGRAND_NON_INTERLOCKED_SOCKETS_FLUSH_MOUNTED_IP66_400.rfa | RFA (0.51Mo)

Agreements & Certificates

 OC / CB-FR_710635/A1 | (0.72Mo)

 LGRP-2015-018-V1-EN.pdf | PDF (0.62Mo)