

Product sheet



LEGRAND

Hinged glass door - for cabinets - IP54 - width 400 x height 400 mm

REF. 047546 | EAN. 3245060475468

> [Visit e-catalogue](#)

Product characteristics

- Atlantic stainless steel and Marina cabinets - equipment
- Hinged glass doors - IP 54 - Anodised aluminium frame - Polycarbonate transparent window, 3 mm stick - Neoprene seal - 455 key lock. 120° opening - Supplied complete with drilling template - For devices on Front panels . Protect the devices and prevent accidental operation - Width : 400 mm - Height : 400 mm - External dim. Width : 50 mm - Window Height : 330 mm - Window Depth : 330 mm - Usable Depth : 42 mm

Documentation

TECHNICAL DOCUMENTATION

→ [042503-00.pdf](#) | PDF (0.07Mo)

Agreements & Certificates

 [LGRP-00279-V01.01-EN.pdf](#) | PDF (1.01Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0432.pdf](#) | PDF (0.08Mo)