

Product sheet



HYPRA LEGRAND

Panel appliance inlet Hypra - IP 44 - 380/415 V~ - 16 A
- 3P+N+E - metal

REF. 052164 | EAN. 3245060521646

[> Visit e-catalogue](#)

Product characteristics

- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prinsinter) LV panel appliance inlets 380 to 415 V~ 50/60 Hz - 16 A 3P+N+E - To be associated with Cat.No 0 522 79 for surface appliance inlets - Metal - 16 A

Documentation

TECHNICAL DOCUMENTATION

-  F00138FR-04.pdf | PDF (1.44Mo)
-  F00138EN-04.pdf | PDF (1.25Mo)
-  2500289-02.pdf | PDF (0.03Mo)

Agreements & Certificates

-  OC / CB-FR_710635/A1 | (0.72Mo)

CAD & Design specs / BIM

-  052174.dwg | DWG (0.1Mo)