

Product sheet



HYPRA LEGRAND

Mobile socket Hypra - IP 44 - 20/25 V~ - 16 A - 2P - rubber

REF. 052481 | EAN. 3245060524814

[> Visit e-catalogue](#)

Product characteristics

- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prinsinter) ELV mobile plugs 20 to 25 V~ - 50/60 Hz - 16 A 2P - Plastic - 16 A

Documentation

TECHNICAL DOCUMENTATION

 F00138FR-04.pdf | PDF (1.44Mo)

 F00138EN-04.pdf | PDF (1.25Mo)

Agreements & Certificates

 OC / CB-FR_710635/A1 | (0.72Mo)

CAD & Design specs / BIM

 052481.dwg | DWG (0.09Mo)