

Product sheet



HYPRA LEGRAND

Mobile socket Hypra - IP 44 - 380/415 V~ - 63 A - 3P+N+E - rubber

REF. 053894 | EAN. 3245060538941

> [Visit e-catalogue](#)

Product characteristics

- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prinsinter) LV mobile sockets 380 to 415 V~ 50/60 Hz - 63 A 3P+N+E - Rubber - 63 A

Documentation

TECHNICAL DOCUMENTATION

 F00138FR-04.pdf | PDF (1.44Mo)

 F00138EN-04.pdf | PDF (1.25Mo)

 LE09817AA.pdf | PDF (0.36Mo)

Agreements & Certificates

 OC / CB-FR_710636 | (0.64Mo)

CAD & Design specs / BIM

 053894.dwg | DWG (0.08Mo)