

Product sheet



LEGRAND

Weatherproof LED portable safety lamp - specially designed for safety interventions in electrical rooms

REF. 060894 | EAN. 3414970531100

> [Visit e-catalogue](#)

Product characteristics

- LED portable lamps
- LED portable safety lamps Weatherproof LED portable safety lamp - Specially designed for safety interventions in electrical rooms - 120° rotating handle - 2 operating modes : - automatic changeover to emergency lighting when mains supply interruption - manual switching of emergency lighting after mains supply interruption - manual switching of emergency lighting after mains supply interruption - Manual selection of lighting mode on push - button : - full power illumination 100 lumens / 1h duration - half power illumination 45 lumens / 3h duration - flashing - OFF - 2 installation modes with docking station : wall - mounting or freestanding - Magnetic Fixing system on the back of the lamp - Locating flashing LED when black - out - Electronic anti - theft function - Ni - Cd built - in battery pack - IP 55 - IK 08 - Power supply (for docking station) : 230 V +/- 10% - 50/60 Hz - Low power consumption : 1.3 W - Class III (lamp only) - Plug - in terminal block for fixed power supply wiring - Also delivered with AC power cord

Documentation

TECHNICAL DOCUMENTATION

→ [LE09193AC.pdf](#) | PDF (0.95Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0913.pdf](#) | PDF (0.05Mo)