

Product sheet



LEGRAND

Bulkhead light - IP44 - IK06 - oval 60 W-E27 -plastic grid screw fixing -grey

REF. 060405 | EAN. 3245060604059

[> Visit e-catalogue](#)

Product characteristics

- IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
- Oval - IP 44 / IK 06 - Polypropylene base - Glass diffuser - Galvanised steel or plastic - Protection wire grid - 3 side knockable entries, for 16, 20 mm - cable - 230 V - 50 Hz - Self - extinguishing : 850 °C - For compact fluorescent lamps - Porcelain lampholder - Screw terminals 12 W - E 27 - Grey - Plastic grid - screw Fixing

Documentation

TECHNICAL DOCUMENTATION

→ [LE12201AA.pdf](#) | PDF (0.46Mo)

Agreements & Certificates

 [LGRP-00521-V01.01-EN.pdf](#) | PDF (0.56Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0901.pdf](#) | PDF (0.09Mo)

 [ex223001_0902.pdf](#) | PDF (0.09Mo)