

Product sheet



LEGRAND

Bulkhead light - IP55 - IK04 - oval - 75 W- E27 - though environments

REF. 060477 | EAN. 3245060604776

> [Visit e-catalogue](#)

Product characteristics

- IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
- IP 55 - IK 04 bulkhead lights for tough environments IP 55 - IK 04 bulkhead lights - Metal/glass bulkhead lights. - For exterior/indoor use - For industrial use. Earth terminal - 3 entries in T. Operating temperature : - min. : - 30 °C - max. : + 35 °C - Can be equipped with metal protection grid for IK 07 protection - E 27 - Oval - for 55 W halogen, 17 W compact fluorescent or 8 W LED lamps - With colourless glass diffuser

Documentation

TECHNICAL DOCUMENTATION

 F00324FR-00.pdf | PDF (0.31Mo)

→ LE11455AA.pdf | PDF (0.14Mo)

Agreements & Certificates

 LGRP-00124-V01.01-EN.pdf | PDF (0.56Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0901.pdf | PDF (0.09Mo)

 ex223001_0902.pdf | PDF (0.09Mo)