

Product sheet



LEGRAND

Bulkhead light Koro - IP54 - IK08 - round - 100
Wincandescent - E27 - white

REF. 062425 | EAN. 3245060624255

> [Visit e-catalogue](#)

Product characteristics

- IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
- IP 54 - IK 08 Plexo rectangular bulkhead lights class II - Polycarbonate diffuser, mounted on hinge - Opening can be reversed Top/Base - Supplied with one Plexo end cap, not assembled - Through wiring or terminal connection (side or rear) - Lampholder mounted on reflector (swivel pull - out type) - Grey base self - extinguishing : 850 °C - For E27 - 55 W halogen, 17 W compact fluorescent or 8 W LED lampsIP 54 - IK 08 - class II - Polycarbonate diffuser, mounted on hinge - Opening can be reversed Right/ Left - Supplied with 1 Plexo end cap, not assembled - Through wiring or terminal connection (side or back) - Through wiring or terminal connection (side or back) - Self - extinguishing at 850 °C - White - E 27 - For E27 70 W halogen, 20 W compact fluorescent or 12 W LED lamps

Documentation

TECHNICAL DOCUMENTATION

- 0064AC511.pdf | PDF (1.31Mo)
- 📄 S000092755FR_1.pdf | PDF (0.53Mo)

Agreements & Certificates

- 📄 LGRP-00120-V01.01-EN.pdf | PDF (0.57Mo)

CATALOGUE PAGE & OTHERS

- 📖 ex223001_0901.pdf | PDF (0.09Mo)
- ⚙️ LG-062425.zip | ZIP (0.03Mo)
- 📖 ex223001_0902.pdf | PDF (0.09Mo)