

Product sheet



PLEXO™ LEGRAND

Plexo™ - 1-gang surface box with 2 membrane glands (2 x 1 entry) - IP55 - Anthracite

REF. 069601L | EAN. 3414971879843

The anthracite waterproof 1-gang box Plexo allows a surface mounting of all Plexo functions (mechanism products). The box conception gives the opportunity to wire the mechanism from the top, bottom, sides or back. For indoor or outdoor use.

> [Visit e-catalogue](#)

Description

The anthracite waterproof 1-gang box Plexo allows a surface mounting of all Plexo functions (mechanism products). The box conception gives the opportunity to wire the mechanism from the top, bottom, sides or back. For indoor or outdoor use.

Product characteristics

- Surface box to install functions supplied in composable mode (mechanism products).
- IP55 : protected against dust and water spary from all directions.
- Plastic materials with reinforced UV protection

The product's benefits

Installation

- A two-part box : a thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring (the flexible part on the back of the product adapts to the shape of the wall) and a frame, to be clipped on the mounting plate.

Avantages

- The box is composed of a mounting plate and a frame. The thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring. The flexible part on the back of the product adapts to the shape of the wall.
- The mechanism is fixed to the mounting plate symmetrically at 90°, allowing cables/tubes to be fed in from the top, bottom, right or left, while maintaining the standard vertical position of the button.

Documentation

TECHNICAL DOCUMENTATION

F03421EN-02.pdf | PDF (1.91Mo)

F03421FR-02.pdf | PDF (1.9Mo)

CAD & Design specs / BIM

BIM-LEGRAND-PLEXO-2025-FRANCAIS.rvt | RVT (135.87Mo)

3D_LG-069601L.stp | IFC (0.77Mo)

BIM-LEGRAND-PLEXO-2025-ENGLISH.rvt | RVT (137.72Mo)

CATALOGUE PAGE & OTHERS

ex223001_0795.pdf | PDF (0.15Mo)

Agreements & Certificates

MEEI-UP 69267307 002 | (1.25Mo)

LGRP-01312-V02.01-FR.pdf | PDF (0.77Mo)

-  LGRP-01292-V02.01-FR.pdf | PDF (0.82Mo)
-  NF App Domestic-NF012_3249/A1 | (0.7Mo)
-  AENOR-030/002621 | (0.71Mo)
-  VDE-40057978 | (1.18Mo)
-  NF App Domestic-NF012_3294/A2 | (0.74Mo)
-  OC / CB-FR_717742 | (0.53Mo)
-  OC / CB-FR_715939 | (0.64Mo)
-  NF App Domestic-NF012_3831/A1 | (0.56Mo)
-  OC / CB-FR_718712/A1 | (0.55Mo)
-  Decl. UE RED-A 4228 A | (0.45Mo)
-  MEEI-UP 69267307 001 | (1.57Mo)
-  OC / CB-FR_720352 | (0.34Mo)
-  LGRP-01513-V02.01-FR.pdf | PDF (0.75Mo)
-  MEEI-UP 69267307 003 | (1.57Mo)
-  Decl. UE RED-A 4044 C | (0.45Mo)
-  OC / CB-FR_719272 | (0.33Mo)
-  OC / CB-FR_715726 | (0.74Mo)