

Product sheet


DLP **LEGRAND**

Snap-on trunking 3 compartments white 50x180mm, length 2m

REF. 075606 | EAN. 3245060756062

> [Visit e-catalogue](#)

Product characteristics

- Delivered with 3 covers, width 45mm
- Wiring capacity : maximum diameter 38mm
- Cross - section : compartment A and C 2442mm² and compartment B 1950mm²
- Compatible with all the functions of Mosaic Program
- IP40 : protected against solid bodies larger 1mm maximum

The product's benefits

Installation

- Fixing by: wall plugs for immediate fixing (cat.no 030899), DLP rapid wall plug (ref 0308 97) or screw, nails...

Usage

- Can be installed in tertiary and residential

Documentation

TECHNICAL DOCUMENTATION

- [LE01020AB.pdf](#) | PDF (0.4Mo)
-  [F00886FR-04.pdf](#) | PDF (1.06Mo)
-  [F00886EN-06.pdf](#) | PDF (1Mo)

CAD & Design specs / BIM

- [BIM-LEGRAND-GOULOTTES-BELGIQUE-2024.rvt](#) | RVT (23.93Mo)
- [BIM-LEGRAND-TRUNKING-EXPORT-2024.rvt](#) | RVT (14.36Mo)
- [BIM-LEGRAND-GOULOTTES-FRANCE-2024.rvt](#) | RVT (13.17Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_1066-1067.pdf](#) | PDF (0.17Mo)
-  [ex223001_1061.pdf](#) | PDF (0.13Mo)

Agreements & Certificates

-  [LGRP-01604-V02.01-EN.pdf](#) | PDF (0.74Mo)
-  [LGRP-01604-V02.01-FR.pdf](#) | PDF (0.71Mo)