

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - Shaver socket - automatic terminals - 5 modules - white

REF. 077586 | EAN. 3245060775865

> [Visit e-catalogue](#)

Product characteristics

- Mosaic™ Programme mechanisms - keyswitches, emergency stop pushbuttons, keycard switches, hotel bedroom indicators, shaver socket
- Shaver socket IP 24 - IK 04 - Conform to EN 60742 and EN 61558 - 2 - Power supply 230 V~ - 50/60 Hz and 1 output 120/220 V~ - Connection via automatic terminals - Equipped with a circuit separation transformer to isolate the user from the mains supply - Protected against overloads and short circuits by built - In thermal relay limiting the available power to 20 VA - Insertion of the plug activates the power supply to the transformer - With integrated support - For flush mounting 2 gang boxes only, 40 mm deep - 5 modules

Documentation

TECHNICAL DOCUMENTATION

 F00894FR-01.pdf | PDF (0.44Mo)

 F00894EN-01.pdf | PDF (0.44Mo)

CAD & Design specs / BIM

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1181.pdf | PDF (0.09Mo)

Agreements & Certificates

 OC / CB-FR_701617 | (0.48Mo)

 ENEC-ENEC_1028 | (0.99Mo)