

# Product sheet



MOSAIC™ LEGRAND

Mosaic™ - RJ45 socket controlled access category 6 shielded STP 2 modules white with red shutter

REF. 076596 | EAN. 3245060765965

> [Visit e-catalogue](#)

## Product characteristics

- RJ45 Cat 6 : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector, and shielded socket to eliminate interference
- 2 modules
- White with red shutter

## Recommendation / Restriction

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

## The product's benefits

### Installation

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

### Usage

- The key lock system let you secure the socket to prevent the connector from damage or external access. Once the cord is plugged, the key is needed to prevent any unintended opening. Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

### Advantages

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

## Documentation

### TECHNICAL DOCUMENTATION



F00949FR-08.pdf | PDF (0.78Mo)

### CATALOGUE PAGE & OTHERS



ex223001\_0986.pdf | PDF (0.11Mo)

→ LE01557AK.pdf | PDF (1.59Mo)

→ LE01557AJ.pdf | PDF (1.55Mo)

 F00949EN-08.pdf | PDF (0.78Mo)

Agreements & Certificates

 LGRP-00945-V02.01-FR.pdf | PDF (0.8Mo)

 LGRP-00945-V02.01-EN.pdf | PDF (0.8Mo)

 AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)

 AoC-PL2\_C6\_STP\_32757\_ac1181031 | (0.08Mo)

 AoC-CL2\_C6\_STP\_32757\_ac1181032 | (0.08Mo)

 ex223001\_1189.pdf | PDF (0.11Mo)