

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - Universal dimmer without neutral 2 wires
125W white

REF. 078407A | EAN. 3414972365451

This universal light dimmer supports all "Dimmable" type bulbs on the market, LEDs, Halogens, Fluocompact, etc. It allows you to create a luminous atmosphere while reducing your energy consumption.

> [Visit e-catalogue](#)

Description


This universal light dimmer supports all "Dimmable" type bulbs on the market, LEDs, Halogens, Fluocompact, etc. It allows you to create a luminous atmosphere while reducing your energy consumption.

Product characteristics

- Allows you to control Dimmable bulbs of the market, LEDs, halogen, compact fluorescent
- Power : 125W max. Dimmable Leds/Fluocompact/Halogen
- Without neutral
- Compatible box depth 40mm
- White

Documentation

TECHNICAL DOCUMENTATION

-  F03676EN-02.pdf | PDF (1.17Mo)
-  F03676FR-02.pdf | PDF (1.18Mo)
-  LE14059AD_2.pdf | PDF (3.54Mo)

Agreements & Certificates

-  OC / CB-HU-005070 | (0.63Mo)

The product's benefits

Installation

- Auxiliary entry for mechanical push-button control

Usage

- Universal dimmer - Upper and lower light adjustment

Avantages

- Universal dimmer. Compatibility with a wide range of "Dimmable" LED bulbs

CATALOGUE PAGE & OTHERS

-  ex223001_1177.pdf | PDF (0.07Mo)