

Product sheet



LEGRAND

Round waterproof floor box with removable lid for wiring devices 4 modules. Stainless Steel finish.

REF. 088061 | EAN. 3414970341341

> [Visit e-catalogue](#)

Product characteristics

- Sealing class IP66 : completely protected against dust and against jets of water of similar force to heavy seas
- Supports a load up to 1 Tonne (closed cover) and resists impacts of energy equivalent to 10 Joules (Protection class IK09) .
- Cable entries pre - cut for several pipe diameters (16, 20 and 25mm).
- Comply with IEC 60-670-1 et 60-670-23 standards.

Recommendation / Restriction

- indoors and outdoors installation

The product's benefits

Installation

- Easy and quick installation thanks to four mounting claws using a screwdriver :- For screed floors: with the auto-adjustable backbox cat.no 088069- For technical floors or elevated deck (thickness of tiles from 15mm to 55mm).

Usage

- Ideal for a long-term use in association with its accessory Cat.No 088062 which ensures an excellent tightness connected cords.Integrates both indoors and outdoors, for public spaces (shopping mall, hotel ...) or residential (terrace, poolside ...).

Avantages

- Secured access: locking with an Allen key (Ideal in public areas or spaces welcoming children).

Documentation

TECHNICAL DOCUMENTATION

- [LE07367AA-04.pdf](#) | PDF (2.77Mo)
- [F02138FR-06.pdf](#) | PDF (3.25Mo)
- [F02138EN-06.pdf](#) | PDF (3.24Mo)

CAD & Design specs / BIM


- [legrand-boites-de-sol-ip66-ik09-FR.rfa](#) | RFA (1.01Mo)
- [Legrand-ip66-ik9-round-floor-boxes-EN.rfa](#) | RFA (1.01Mo)
- [Legrand_IP_66_floorbox_4_modules_R2019.rvt](#) | RVT (2.9Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_1161.pdf](#) | PDF (0.11Mo)
- [ex223001_1163.pdf](#) | PDF (0.1Mo)

Agreements & Certificates

- [LGRP-00110-V02.01-EN.pdf](#) | PDF (0.74Mo)

-  3D_LG-088061.stp | IFC (24.51Mo)
- Legrand-ip66-ik9-round-floor-box-benelux.rfa | RFA (1.01Mo)
- Legrand_IP_66_Boite_de_sol_4_modules_R2019.rvt | RVT (3.01Mo)