

Product sheet



MOSAIC™ LEGRAND

Floor box 3 modules for integration - To be fitted with 1 Mosaic 2-module 2P+E socket and 1 Mosaic 1-module RJ 45 socket

REF. 089644 | EAN. 3245060896447

> [Visit e-catalogue](#)

Product characteristics

- Floor boxes are in plastic PC/ABS RAL 7031
- Color grey RAL 7031
- IP20 - IK07
- 2 covers of independent exit for low or high current cables
- Comply with norm CEI 60670-23

Recommendation / Restriction

- For installation in concrete floor: it is necessary to stop the hole of plastic floor boxes with adhesive tape or paperboard for example before put the concrete - Minimum height required : 80mm - Tile thickness between 6 and 28mm - Temperature of use, transport and storage: -5° à +60°

The product's benefits

Installation

- For renovation in low depth raised floor or in concrete floor (height $\geq$ 80mm)

Advantages

- To supply from the floor the workstation in power and data

Documentation

TECHNICAL DOCUMENTATION

→ [LE02183AA.pdf](#) | PDF (2.61Mo)

 [F00888FR-00.pdf](#) | PDF (0.18Mo)

 [F00888EN-00.pdf](#) | PDF (0.18Mo)

CAD & Design specs / BIM

[Legrand-3-modules-floor-boxes-EN.rfa](#) | RFA (1Mo)

[Legrand-3-modules-floor-boxes-benelux.rfa](#) | RFA (1Mo)

[Legrand-boites-de-sol-3-modules-FR.rfa](#) | RFA (1Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_1165.pdf](#) | PDF (0.05Mo)