

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - Support - with site protection - for 2 modules

REF. 080251 | EAN. 3245060802516

> [Visit e-catalogue](#)

Product characteristics

- supports with site protection - For 2 modules

Documentation

TECHNICAL DOCUMENTATION

 F00440FR-02.pdf | PDF (0.66Mo)

 F00440EN-02.pdf | PDF (0.66Mo)

CAD & Design specs / BIM

BIM-LEGRAND-CELIANE-2025-FRANCAIS.rvt | RVT (169.55Mo)

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

 3D_LG-080251.stp | IFC (14.91Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1204.pdf | PDF (0.18Mo)

Agreements & Certificates

 NF App Domestic-NF012_4571/M1 | (1Mo)

 OC / CB-FR_715034/M1 | (0.98Mo)

 LGRP-00418-V02.01-FR.pdf | PDF (0.73Mo)

 OC / CB-FR_700177/A1 | (0.71Mo)

 LGRP-01081-V02.01-FR.pdf | PDF (0.86Mo)

 B.B.J-B/12/006/24 | (3.34Mo)

 B.B.J-B/12/048/21 | (2.83Mo)

 LGRP-02143-V01.01-FR.pdf | PDF (0.81Mo)

 LGRP-00046-V01.01-FR.pdf | PDF (0.74Mo)

 OC / CB-DE 2-043294 | (0.63Mo)

 OC / CB-FR 630163B/A1 | (0.56Mo)

 LGRP-01937-V01.01-FR.pdf | PDF (0.83Mo)

 OC / CB-620080 | (2.41Mo)

 OC / CB-FR_709693/M1 | (0.67Mo)

 OC / CB-FR_707308/A3 | (4.23Mo)

 LGRP-00945-V02.01-EN.pdf | PDF (0.8Mo)

	OC / CB-FR_720392 (0.4Mo)
	OC / CB-HU-005377 (0.56Mo)
	LGRP-01899-V01.01-FR.pdf PDF (0.86Mo)
	NF App Domestic-NF012_1945 (0.74Mo)
	LGRP-00644-V02.01-FR.pdf PDF (0.67Mo)
	NF App Domestic-NF012_2201/A2 (1.3Mo)
	LGRP-00700-V01.01-FR.pdf PDF (0.65Mo)
	B.B.J-B/12/047/21 (2.9Mo)
	AENOR-030/002285 (0.47Mo)
	LGRP-01897-V01.01-FR.pdf PDF (0.84Mo)
	B.B.J-B/12/041/21 (2.84Mo)
	LGRP-01898-V01.01-FR.pdf PDF (0.89Mo)
	NF App Domestic-NF012_2666/M1 (1.1Mo)
	NF App Domestic-NF012_2513/A1 (0.91Mo)
	NF App Domestic-NF012_4236/A1 (0.5Mo)
	OC / CB-FR_705591/A3 (0.73Mo)
	OC / CB-HU-005072 (0.6Mo)
	OC / CB-HU-005070 (0.63Mo)
	OC / CB-FR_717745 (0.46Mo)
	LGRP-01612-V01.01-FR.pdf PDF (0.73Mo)
	NF App Domestic-NF012_2275/A2 (0.96Mo)
	LGRP-02144-V01.01-EN.pdf PDF (0.88Mo)
	NF App Domestic-NF012_4512/M1 (0.91Mo)
	B.B.J-B12/005/24 (4.62Mo)
	MEEI-UP 69267544 002 (1.23Mo)
	OC / CB-HU-005201 (0.76Mo)
	OC / CB-DE 2-043291 (0.63Mo)
	LGRP-01912-V01.02-FR.pdf PDF (0.81Mo)
	LGRP-00562-V01.01-FR.pdf PDF (0.67Mo)
	LGRP-01330-V02.01-FR.pdf PDF (0.81Mo)
	LGRP-01024-V02.01-FR.pdf PDF (0.85Mo)
	OC / CB-FR_707532/M1 (1.51Mo)
	LGRP-01210-V01.01-EN.pdf PDF (0.67Mo)
	LGRP-01211-V01.01-EN.pdf PDF (0.71Mo)
	LGRP-01212-V01.01-EN.pdf PDF (0.68Mo)
	LGRP-02141-V01.01-EN.pdf PDF (0.85Mo)
	LGRP-00701-V02.02-FR.pdf PDF (0.8Mo)

	MEEI-UP 69267544 001 (2.21Mo)
	OC / CB-645761B (0.38Mo)
	OC / CB-HU-005098-M1 (0.85Mo)
	OC / CB-FR_709181 (0.68Mo)
	LGRP-00992-V01.01-FR.pdf PDF (0.69Mo)
	LGRP-01192-V01.01-FR.pdf PDF (0.75Mo)
	OC / CB-HU-005009-A1/M1 (0.73Mo)
	LGRP-00991-V01.01-FR.pdf PDF (0.71Mo)
	LGRP-01910-V01.01-FR.pdf PDF (0.84Mo)
	LGRP-00418-V02.01-EN.pdf PDF (0.73Mo)
	LGRP-00942-V02.01-FR.pdf PDF (0.86Mo)
	OC / CB-FR_709703 (1.06Mo)
	OC / CB-620094 (1.58Mo)
	LGRP-02051-V01.01-FR.pdf PDF (0.84Mo)
	NF App Domestic-NF012_1947 (0.64Mo)
	OC / CB-645761D (0.38Mo)
	OC / CB-FR_721500 (1.81Mo)
	OC / CB-630164B/A1 (0.56Mo)
	OC / CB-FR_707077/M1 (0.43Mo)
	OC / CB-DE 2-039435-M1 (0.63Mo)
	Decl. UE RED-A 4025 A (0.62Mo)
	LGRP-01330-V02.01-EN.pdf PDF (0.82Mo)
	NF App Domestic-NF012_4239 (0.53Mo)
	LGRP-01279-V01.02-EN.pdf PDF (0.7Mo)
	LGRP-01911-V02.01-FR.pdf PDF (0.83Mo)
	OC / CB-HU-005022-M1 (0.7Mo)
	IRAM-DC-E-E100-003.1M2 (2.18Mo)