

# Product sheet



MOSAIC™ LEGRAND

Mosaic™ - Support - with site protection - for 2 modules with clips or claws

REF. 080261 | EAN. 3245060802615

> [Visit e-catalogue](#)

## Product characteristics

- supports with site protection - For 2 modules with clips or claws (length 27 mm)

## Documentation

### TECHNICAL DOCUMENTATION

 F00440FR-02.pdf | PDF (0.66Mo)

 F00440EN-02.pdf | PDF (0.66Mo)

### CAD & Design specs / BIM

BIM-LEGRAND-CELIANE-2025-FRANCAIS.rvt | RVT (169.55Mo)

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_1204.pdf | PDF (0.18Mo)

### Agreements & Certificates

 NF App Domestic-NF012\_4571/M1 | (1Mo)

 OC / CB-FR\_700177/A1 | (0.71Mo)

 B.B.J-B/12/006/24 | (3.34Mo)

 NF App Domestic-NF012\_4769 | (0.91Mo)

 B.B.J-B/12/048/21 | (2.83Mo)

 OC / CB-FR\_707532/M1 | (1.51Mo)

 OC / CB-FR\_709693/M1 | (0.67Mo)

 OC / CB-FR\_722215 | (2.36Mo)

 MEEI-UP 69267544 001 | (2.21Mo)

 OC / CB-FR\_720392 | (0.4Mo)

 OC / CB-HU-005377 | (0.56Mo)

 OC / CB-HU-005009-A1/M1 | (0.73Mo)

 OC / CB-FR\_722156 | (1.77Mo)

 B.B.J-B/12/047/21 | (2.9Mo)

 AENOR-030/002285 | (0.47Mo)

 B.B.J-B/12/041/21 | (2.84Mo)

|                                                                                   |                                          |
|-----------------------------------------------------------------------------------|------------------------------------------|
|  | OC / CB-FR_709703   (1.06Mo)             |
|  | LGRP-00561-V02.01-FR.pdf   PDF (0.77Mo)  |
|  | NF App Domestic-NF012_2666/M1   (1.1Mo)  |
|  | NF App Domestic-NF012_2513/A1   (0.91Mo) |
|  | NF App Domestic-NF012_4236/A1   (0.5Mo)  |
|  | OC / CB-FR_721500   (1.81Mo)             |
|  | OC / CB-FR_707077/M1   (0.43Mo)          |
|  | NF App Domestic-NF012_2275/A2   (0.96Mo) |
|  | NF App Domestic-NF012_4239   (0.53Mo)    |
|  | B.B.J-B12/005/24   (4.62Mo)              |
|  | OC / CB-HU-005022-M1   (0.7Mo)           |
|  | MEEI-UP 69267544 002   (1.23Mo)          |