

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - Support - for 2 x 6, 2 x 8 or 2 x 3 x 2 modules

REF. 080266 | EAN. 3245060802660

> [Visit e-catalogue](#)

Product characteristics

- supports with site protection - For 2 x 6, 2 x 8 or 2 x 3 x 2 modules - Without site protection

Documentation

TECHNICAL DOCUMENTATION

 F00440FR-02.pdf | PDF (0.66Mo)

 F00440EN-02.pdf | PDF (0.66Mo)

CAD & Design specs / BIM

BIM-LEGRAND-CELIANE-2025-FRANCAIS.rvt | RVT (169.55Mo)

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1204.pdf | PDF (0.18Mo)

Agreements & Certificates

 NF App Domestic-NF012_4571/M1 | (1Mo)

 OC / CB-FR_722156 | (1.77Mo)

 B.B.J-B/12/006/24 | (3.34Mo)

 LGRP-00046-V01.01-FR.pdf | PDF (0.74Mo)

 AENOR-030/002285 | (0.47Mo)

 OC / CB-FR_707532/M1 | (1.51Mo)

 OC / CB-FR_709703 | (1.06Mo)

 LGRP-00045-V01.01-FR.pdf | PDF (0.75Mo)

 NF App Domestic-NF012_2666/M1 | (1.1Mo)

 NF App Domestic-NF012_2513/A1 | (0.91Mo)

 OC / CB-FR_709693/M1 | (0.67Mo)

 OC / CB-FR_721500 | (1.81Mo)

 OC / CB-FR_707308/A3 | (4.23Mo)

 MEEI-UP 69267544 001 | (2.21Mo)

 OC / CB-HU-005377 | (0.56Mo)

 NF App Domestic-NF012_2275/A2 | (0.96Mo)

-  NF App Domestic-NF012_4512/M1 | (0.91Mo)
-  OC / CB-HU-005009-A1/M1 | (0.73Mo)
-  B.B.J-B12/005/24 | (4.62Mo)
-  OC / CB-HU-005022-M1 | (0.7Mo)
-  NF App Domestic-NF012_2201/A2 | (1.3Mo)
-  MEEI-UP 69267544 002 | (1.23Mo)