

Product sheet



BATIBOX LEGRAND

Batibox - Flush mounting box - 4 gang German std - depth 50 mm - dry partitions

REF. 080054 | EAN. 3245060800543

> [Visit e-catalogue](#)

Product characteristics

- Multi-gang boxes - For wiring equipment using screws - Drilling diameter 67 mm - Supplied with 1 removable divider for accomm odating extended functions For 60 and 71 mm fixing centres - Compatible with : Arteur, Galea Life, Mosaic, Valena, Niloé, Kaptika - Depth 50 - 4-gang or 8/10 modules - Horizontal or vertical use

Documentation

TECHNICAL DOCUMENTATION

 F00447EN-01.pdf | PDF (1.42Mo)

 F00447FR-01.pdf | PDF (1.34Mo)

CAD & Design specs / BIM

 3D_LG-080054.stp | IFC (29.99Mo)

BIM-LEGRAND-CELIANE-2025-FRANCAIS.rvt | RVT (169.55Mo)

BIM-BTICINO-LIVING-NOW-2025-ENGLISH.rvt | RVT (152.05Mo)

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-BTICINO-LIVING-NOW-2025-FRANCAIS.rvt | RVT (69.92Mo)

BIM-LEGRAND-DOOXIE-2025-FRANCAIS.rvt | RVT (53.54Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0810.pdf | PDF (0.17Mo)

 ex223001_0811.pdf | PDF (0.2Mo)

Agreements & Certificates

 NF App Domestic-NF012_4462/A1 | (0.62Mo)

 LGRP-01002-V02.01-FR.pdf | PDF (0.8Mo)

 OC / CB-FR_705863/M1 | (0.57Mo)