

Product sheet



MOSAIC™ LEGRAND

Receptacle for floor socket Arteur/Mosaic - rectangular version -Stainless Steel

REF. 089702 | EAN. 3245060897024

Floor sockets

> [Visit e-catalogue](#)

Description

Floor sockets

Product characteristics

- Receptacles for floor sockets - Extra slim plate IP 44 - IK 08 - Equipped with a 180° opening flap - Extra flat finish: thickness 2 mm - Lighting base of receptacle by white LED - To be equipped with 2 modules square version Arteur or Mosaic functions: - socket outlets without cover, German, Euro-US, Swiss, Danish, Israeli and French standards - Double USB chargers - RJ 11 and RJ 12 sockets, Television sockets, RJ 45 sockets UTP, FTP and STP without controlled access - loudspeaker sockets - HDMI sockets or HD 15 sockets without jackRectangular receptacle - Stainless steel

Recommendation / Restriction

- Can be installed outdoors if protected from the elements (e.g. covered terrace). Mandatory : - Use Legrand flush-mounting boxes: for concrete reference 0801 88 and for multi-material reference 0819 88 - Install the insulation plugs supplied with the multi-material flush-mounting box, reference 0819 88.

Documentation

TECHNICAL DOCUMENTATION

 F01511EN-07.pdf | PDF (0.97Mo)

 F01511FR-07.pdf | PDF (0.97Mo)

 LE04522AD.pdf | PDF (0.86Mo)

CAD & Design specs / BIM

 3D_LG-089702.stp | IFC (46.12Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1167.pdf | PDF (0.64Mo)

Agreements & Certificates

 LGRP-01153-V02.01-FR.pdf | PDF (0.77Mo)

 NF App Domestic-NF012_3369 | (0.55Mo)