

Product sheet



PLEXO™ LEGRAND

Square Plexo box with 7 direct entry membrane glands
- IP55 IK07 - 80x80x45 mm - grey RAL 7035

REF. 092012 | EAN. 3245060920128

[> Visit e-catalogue](#)

Product characteristics

- Plexo boxes IP 55 - IK 07 - with direct entry membrane glands - 650°C - IP 55 - IK 07 - Resistance to incandescent wire 650°C - For use as junction boxes in any type of normal installation circuit - Operating temperature : - 25 to +40°C - Interchangeable membrane glands with direct entries for IRL tubes up to 16 and R02V cables, with marked cut - out for IRL tube greater than 16 - Captive cover with tie. Space for marking on both sides of the cover. Fixing with vertical level adjustment. Class II is ensured by protective caps (supplied) for the Fixing screws - boxes without halogenated flame retardants (European Directive RoHS 2002/95/EC)
- Square boxes - Can be fixed using a tool such as a Pulsa 700 E nail gun - 7 membrane glands 65 x 65 x 40 mm - Grey RAL 7035 - Accepted cable and tube : 4 to 20 mm - Clippable covers

Documentation

TECHNICAL DOCUMENTATION

-  [F01039EN-03.pdf](#) | PDF (1.16Mo)
-  [FT0745_FT_LCM_PLASTIC.pdf](#) | PDF (2.1Mo)
-  [F01039FR-03.pdf](#) | PDF (1.19Mo)


CAD & Design specs / BIM

-  [3D_LG-092012.stp](#) | IFC (0.36Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0801.pdf](#) | PDF (0.1Mo)

Agreements & Certificates

-  [LGRP-01610-V02.01-FR.pdf](#) | PDF (0.76Mo)
-  [OC / CB-FR_715099](#) | (0.51Mo)