

# Product sheet



PLEXO™ LEGRAND

Box Plexo - IP 55 - IK 07 - 130x130x74 - 10 entry membrane glands

REF. 092032 | EAN. 3245060920326

> [Visit e-catalogue](#)

## Product characteristics

- Plexo™ boxes IP 55 - IK 07 - with direct entry membrane glands - 750 °C - Resistance to glow wire test : 750 °C (EN 60695 2 - 11) - Operating temperature : - 25 °C to + 40 °C - Interchangeable membrane glands with direct entry - Captive cover with clippable tie between box and cover except boxes 310 x 240 and 360 x 270 - Cover opens/closes with a 1/4 turn of a regular screwdriver, marking 0 and I - Class II is ensured by protection caps (supplied) for the attachment screws Square boxes - Grey RAL 7035130 x 130 x 74 mm - 10 glands - Ø cables and tubes accepted 4 to 25 mm

## Documentation

### TECHNICAL DOCUMENTATION

 [fa343afr.pdf](#) | PDF (0.03Mo)

### Agreements & Certificates

 [LGRP-01611-V02.01-FR.pdf](#) | PDF (0.78Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0804-0805.pdf](#) | PDF (0.32Mo)

 [ex223001\\_0802.pdf](#) | PDF (0.07Mo)