

Product sheet



PLEXO™ LEGRAND

Compact Plexo box with 10 membrane glands - IP55
IK07 - 80x43x34mm - grey RAL 7035

REF. 092004 | EAN. 3414971401754

> [Visit e-catalogue](#)

Product characteristics

- Plexo boxes IP 55 - IK 07 - with direct entry membrane glands - 650°C - IP 55 - IK 07 - Resistance to incandescent wire 650°C - For use as junction boxes in any type of normal installation circuit - Operating temperature : - 25 to +40°C - Interchangeable membrane glands with direct entries for IRL tubes up to 16 and R02V cables, with marked cut - out for IRL tube greater than 16 - Captive cover with tie. Space for marking on both sides of the cover. Fixing with vertical level adjustment. Class II is ensured by protective caps (supplied) for the fixing screws - boxes without halogenated flame retardants (European Directive RoHS 2002/95/EC)
- Compact box 80 x 43 x 34 mm - Grey - RAL 7035 - Ideal for confined spaces - Clippable covers - 10 membrane glands - Accepted cable and tube : 7 to 16 mm

Documentation

TECHNICAL DOCUMENTATION

 F02789EN-01.pdf | PDF (0.72Mo)

 F02789FR-01.pdf | PDF (0.72Mo)

CAD & Design specs / BIM

 3D_LG-092004.stp | IFC (17.2Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0801.pdf | PDF (0.1Mo)

Agreements & Certificates

 OC / CB-FR_715099 | (0.51Mo)