

# Product sheet



## LEGRAND

Switched mode modular power supply 12v - 24w

REF. 146711 | EAN. 3414970971500

> [Visit e-catalogue](#)

## Product characteristics

- Switching mode power supplies - single-phase - Conform to standards UL 508, UL 60950, EN 61558 - 2 - 16 and IEC EN 60950 - 1, EN 55022 class B, EN 61000 - 3 - 2, EN 61000 - 3 - 3, EN 61000 - 6 - 2 and EN 61204 - 3 - Operating frequency : 50/60 Hz - Output voltage present indicator - Output voltage adjustment potentiometer on front panel - Integrated short - circuit and overload protection - For mounting on a symmetrical rail depth 7.5 mm and 15 mm
- Single-phase - 12 - 92 W - No - load power consumption - Adjustable output voltageInput voltage : 100 to 240 V~ Output voltage : 12 V= - Nominal power : 24 W - Rated current : 2 A - Setting range : 10,8 to 13.8 V - Number of modules : 2

## Documentation

### TECHNICAL DOCUMENTATION

- [LE09915AA-00.pdf](#) | PDF (0.2Mo)
-  [F02467FR-01.pdf](#) | PDF (0.16Mo)
-  [F02467EN-01.pdf](#) | PDF (0.18Mo)

### CAD & Design specs / BIM

-  [146711.dwg](#) | DWG (0.1Mo)

### CATALOGUE PAGE & OTHERS

-  [ex223001\\_0111.pdf](#) | PDF (0.26Mo)

### Agreements & Certificates

-  [UL listed cULus-E223674](#) | (0.04Mo)