

Product sheet



LEGRAND

Switched mode modular power supply 24v - 36w

REF. 146722 | EAN. 3414970971562

> [Visit e-catalogue](#)

Product characteristics

- Switching mode power supplies - single-phase - Conform to standards UL 508, UL 60950, EN 61558 - 2 - 16 and IEC EN 60950 - 1, EN 55022 class B, EN 61000 - 3 - 2, EN 61000 - 3 - 3, EN 61000 - 6 - 2 and EN 61204 - 3 - Operating frequency : 50/60 Hz - Output voltage present indicator - Output voltage adjustment potentiometer on front panel - Integrated short - circuit and overload protection - For mounting on a symmetrical rail depth 7.5 mm and 15 mm
- Single-phase - 12 - 92 W - No - load power consumption - Adjustable output voltageInput voltage : 100 to 240 V~ Output voltage : 24 V= - Nominal power : 36 W - Rated current : 1.5 A - Setting range : 21.6 to 29 V - Number of modules : 2

Documentation

TECHNICAL DOCUMENTATION

- LE09915AA-00.pdf | PDF (0.2Mo)
- F02467FR-01.pdf | PDF (0.16Mo)
- F02467EN-01.pdf | PDF (0.18Mo)

CAD & Design specs / BIM

- 146711.dwg | DWG (0.1Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0111.pdf | PDF (0.26Mo)

Agreements & Certificates

- UL listed cULus-E223674 | (0.04Mo)