

# Product sheet



## LEGRAND

Emergency shutdown control device - 2 NO/NC - 5 A - 24 V= - RAL 9003

REF. 138073 | EAN. 3414970520579

> [Visit e-catalogue](#)

## Product characteristics

- Safety boxes 90 series - for fire detection and fire alarm system, emergency exit, extinguishing system, remote switching
- Manual call points (MCP) - IP 30 - IK 07 - Surface - mounting or flush-mounting (IP 30) - Dimensions : 90x90x57 mm (surface - mounting with its base) or 90x90x24 mm (flush-mounting with flush boxes for wiring devices - drilling diameter 67 mm - for 60 mm Fixing centres) - Can be fitted on trunking Cat. Nos 0 104 63/64, 35x105 mm or 50x105 mm, with the universal support Cat. No 0 109 13 - Call by pressing the membrane (pressure 2.5 kg) with clear display of the call position - Reset on Front of device, with special key Cat. No 0 380 38 (supplied with the product) - Possibility to add an optional mechanical status indicator Cat. No 1 380 93 to provide additional signalling - Can receive a sealable cover Cat.No 0 380 97 Emergency shutdown control devices - Color of the mechanical enclosure : white RAL 9003 - Emergency shutdown control device - 2 contacts - Equipped with 2 NO/NC contacts 5 A 24 VDC - Second contact can be used to trigger a technical alarm

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE07337AC.pdf](#) | PDF (2.95Mo)

### Agreements & Certificates

 [LGRP-00144-V01.01-EN.pdf](#) | PDF (0.61Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0919.pdf](#) | PDF (0.07Mo)